


Series 7777DVP Durafet III Electrode with Vario Pin Connector for In-line Tee or Immersion Mounting

Model Selection Guide

- Includes Electrode and Mounting
- Features state-of-the-art non-glass, ISFET technology
- The Durafet III with UDA cable can only be used with the UDA2182 (Direct pH Input)
- The Durafet III with Cap Adapter cable can be used only with the following instruments:
 - UDA2182 (Preamp Input)
 - APT2000 Transmitter
 - APT4000 Analyzer
- Suitable for in-line or immersion mounting
- 3/4" Threaded connections at top and bottom of electrode
- Combination measuring and reference electrode
- Instruction books on CD included



Instructions

- Select the desired Key Number. The arrow to the right marks the selection available.
- Make one selection each per table using the column below the proper arrow.
- A dot (•) denotes unrestricted availability.

Key Number I II III IV

- - - - 000

KEY NUMBER

Description	Selection	Availability
7777DVP Durafet III Electrode w/Vario Pin Connector In-line or Immersion Mtg.	07777DVP	↓

TABLE I - Mounting Type, Temperature Sensor, Part No.

Mounting	Temperature Sensor	Electrode P/N		
Immersion (w/Tip Guard)	8550 Ohm Thermistor	51453503-505	01	•
	1000 Ohm RTD	51453503-506	02	•
In-Line (w/o Tip Guard)	8550 Ohm Thermistor	51453503-501	03	•
	1000 Ohm RTD	51453503-502	04	•

0777DVP

TABLE II - Instrumentation to Sensor Cables

Cable length	Cable Type	Part Number	Selection	
None			00	•
20 ft (6,10 m)	UDA2182	50001391-501	01	•
50 ft (15,24 m)	UDA2182	50001391-502	02	•
20 ft (6,10 m)	Cap Adapter	51453388-501	04	•
50 ft (15,24 m)	Cap Adapter	51453388-502	05	•

TABLE III - Options

Tagging	None	00 __	•
	Linen Customer I.D. Tag - 3 lines, 22 characters/line	LT __	•
	Stainless Steel Customer I.D.Tag - 3 lines, 22 characters/line	SS __	•
Certifications	None	-- 00	•
	Calibration & Conformance	-- CC	•

TABLE IV - Factory Use

Factory Use Only		000	•
------------------	--	-----	---

Series 7777DVP

Accessories and Replacement Parts

Note:

For replacement electrodes see Replacement Electrodes Price List, Page RE-1 & 2.

Description	Part Number
pH Buffer Solutions	
4	31103001-501
7	31103002-501
9	31103003-501
Smooth Electrode Tip - In-line Mounting	51204993-501
Guarded Tip - Immersion Mounting	51204992-501
Special CPVC pipe tee for 3/4" in-line mounting	31120167-501
Cap Adapter Cables	
20 foot length (6,10 meters)	51453388-501
50 foot length (15,24 meters)	51453388-502
UDA2182 Cables	
20 foot length (6,10 meters)	50001391-501
50 foot length (15,24 meters)	50001391-502
Instruction Manuals	
CD with Manuals	51453555-501
Paper Manual - 7777 DVP Mounting	70-82-25-116
Paper Manual - Durafet III pH Electrode	70-82-25-115
Durafet Cap Adapter Junction Box and Terminals	50034477-501
Durafet Cap Adapter Extension Cables	
20 feet	50033807-501
50 feet	50033807-502
100 feet	50033807-503
200 feet	50033807-504
Durafet Gel Refill Kit	51205807-502